



## Thread "No Go" plug gauge for MultiCheck Digital, Threads: M20



### Order data

Order number	486516 M20
GTIN	4046122621187
Item class	48B

### Description

#### Standard:

Toleranzen und Abmaße nach **DIN ISO 1502**.

#### Suitable for:

Base unit 486511 size 12-20, measuring sleeve No. 486512 size 12-20 and protective sleeve No. 486515 size, M12 up to M20.

### Technical description

Thread type	M
Standard	DIN 13
Thread	M20
Type of gauge	"Go" plug gauge
Thread pitch	2.5 mm
Test certificate	Manufacturer's test certificate
Calibration	Price on request
Type of product	Thread NoGo plug gauge

### Services

Calibration "Go" / "No Go" thread plug gauge maximum Ø 60 mm	028500 60
--	-----------

DAkKS calibration "Go" / "No Go" thread plug gauge  
maximum  $\varnothing$  90 mm

028540 90