

TRICOFLEX**Braided hose, transparent PVC, Length 50 m, Hose internal Ø: 9mm****Order data**

Order number	080042 9
GTIN	3506110929738
Item class	08A

Description**Version:**

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.
TCN-AL, flexible pressure-resistant hose with long working life. High chemical resistance.
Operating pressure 15 bar. Foodstuffs approved (VO/2011 - category A/B/C).

Technical description

Colour	transparent
Hose length	50 m
Hose external Ø	15 mm
Hose internal Ø	9 mm
Material	PVC hose, three-layer with polyester fibre reinforcement
Foodstuffs approved (VO/2011)	yes
maximum operating pressure	15 bar
Temperature range	-15 - 60 °C

Product name attribute	Length 50 m
Type of product	Hose