

Garant GRIDLINE

**Janitor's cabinet Width 30G with plain sheet metal swing doors, Height mm /
Type: 2000-2****Order data**

Order number	987030 2000-2
GTIN	4062406588519
Item class	9GI

Description**Version:**

Universal cabinet for storing cleaning materials, cleaning devices and clothing. Mountings for galvanised shelves at 25-mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a **cylinder lock**. Levelling base with 4 individually adjustable feet to compensate for unevenness in the floor. Shelf load capacity 25 kg. Holes 9×9 mm on a 37 mm grid on the partition housing, for **mounting Easyfix hooks and holders** (in Group 95).

Supplied with:

Practical continuous division with 4 shelves, width 13G. Additional shelf width 13G with clothes hook strip (with 3 hooks).

Supplied with:

Clothes hook strip no. 940610: 1

Colour:

Body light grey RAL 7035, doors signal blue RAL 7016 **powder-coated**.

Note:

The janitor's cabinets are dimensionally compatible with all GridLine cabinets of 20G in depth and can be combined with them as required. Further accessories such as shelves and drawers can be found in Group 94.

Technical description

Depth in G	20
Height	2000 mm
Depth	500 mm
Width in G	30
Usable height	1840 mm
Weight	104 kg
Width	750 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Janitor's cabinet

Accessories

Clothes hook rack for cabinet / compartment width in G 30	940610 30
---	-----------