

Garant UNILINE**CLEANING Tower, H-shape equipped, mobile, Type: L****Order data**

Order number	987123 L
GTIN	
Item class	9GC

Description**Version:**

Modular cleaning tower for direct access to cleaning devices. The CLEANING Tower H-shape, asymmetrical, is completely equipped with 2 recycling collection bins and paper roll holders. All outer walls and the centre partition have perforated panels on all sides \square 9x9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Anthracite-coloured attachment with cleaning pictogram provides quick visualisation. Optional lockable doors offer the facility for secure storage. The door cannot be combined in conjunction with a paper roll holder.

Supplied with:

CLEANING Tower No. 987103 size L; 2 pcs. No. 987110 size 45; 1 pc. size 955499 size W1.
With 4 castors, \varnothing 125 mm, 2 with parking brake.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

Suitable paper wipes can be found under No. 089103 size W, 089105 size W, 089127 size W in the Hoffmann Catalogue Volume 2 or in our eShop.

Technical description

Usable width	690 mm
Height	2290 mm
Width	750 mm
Wheel Ø	125 mm
Depth	750 mm
Safe working load	150 kg
Series	CLEANING Tower UNI Line
Weight	115 kg
Usable depth	180/ 330 mm
Hoffmann perforated panel grid interval	9×9
Type of product	Cleaning station

Accessories

Recycling collection bin, 45 litre Capacity 45 l	987110 45
CLEANING Tower, H-shapemobile Type L	987103 L
Set of wheels for UNI Line, 4 pieces Type 1	955459 1
Holder set with paper roll holder Type W1	955499 W1
UNI Line push handle Type 1	955496 1
CLEANING Tower, H-shapestationary Type L	987102 L
UNI Line pictogram Type CLEANING	955474 CLEANING