



Carbide-tipped hammer drill set "MX4", Drill Ø: 5-12mm



Order data

Order number	789061 5-12
GTIN	4058546348199
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. In a plastic case.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **4-flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Content:

Hammer drill No. 789050: 1 pc. each
size 5; 6 length 110 mm;
size 6; 8; 8; 10; 12 length 160 mm

Technical description

Drill Ø	5 - 12 mm
Number of cutting edges Z	4
Packaging	Plastic case

Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

Accessories

Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 6X160 mm	789050 6X160
Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 12X160 mm	789050 12X160
Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 6X110 mm	789050 6X110
Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 5X110 mm	789050 5X110
Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 8X160 mm	789050 8X160
Carbide-tipped hammer drill "MX4" SDS-plus Øxoverall length 10X160 mm	789050 10X160