

3M Scotch-Brite™

**Bristle-Brush type C Ø 25 mm Set 24 pieces, shank Ø 3 mm., RB-ZB, Grit: 50****Order data**

Order number	573545 50
GTIN	50048011276118
Item class	53M

**Description****Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

Removable mandrel (**shank Ø 3 mm**). Segments can be combined to make up any desired brush width.

With curved bristles (type C) for use on **profiled surfaces**.

**Application:**

Ensure the correct direction of rotation.

Requires no accessories for use on straight grinders or flexible shafts.

**On virtually all materials, with the highest possible safety.** Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

**Supplied with:**

24 individual segments (approx. 1.6 mm wide) **including mandrel** with shank Ø 3 mm.

**Technical description**

maximum speed	35000 min <sup>-1</sup>
Brush Ø D <sub>1</sub>	25 mm
Shank Ø D <sub>s</sub>	3 mm
Colour	green
Grit	50
Brush width	1.6 - 10 mm
Grinding medium code	Ceramic

Product name attribute	RB-ZB
Manufacturer's designation	RB-ZB
Type of product	Wheel brush