

**TRICOFLEX****Braided hose, transparent PVC, Length 50 m, Hose internal Ø: 13mm****Order data**

Order number	080042 13
GTIN	3506110938211
Item class	08A

**Description****Version:**

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.  
TCN-AL, flexible pressure-resistant hose with long working life. High chemical resistance.  
Operating pressure 15 bar. Foodstuffs approved (VO/2011 - category A/B/C).

**Technical description**

Material	PVC hose, three-layer with polyester fibre reinforcement
Colour	transparent
Hose external Ø	20 mm
Hose length	50 m
Hose internal Ø	13 mm
maximum operating pressure	15 bar
Foodstuffs approved (VO/2011)	yes
Temperature range	-15 - 60 °C

Product name attribute	Length 50 m
Type of product	Hose