

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal swing door,
Height: 900mm****Order data**

Order number	942701 900
GTIN	4062406595494
Item class	9GI

Description**Version:**

Empty cabinet in 30×28G. Suitable drawers: 26×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	750 mm
Electronic locking system can be retrofitted	yes

Height	900 mm
Type of cabinet	Base cabinet
Width in G	30
Depth	700 mm
Handle positioning	top
Cabinet fronts	Plain sheet metal swing door
ComfortClose	no
Usable height	745 mm
Depth in G	28
Weight	59 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------