

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door,
Height: 800mm****Order data**

| | |
|--------------|---------------|
| Order number | 942745 800 |
| GTIN | 4062406595869 |
| Item class | 9GI |

Description**Version:**

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately). Mountings for shelves at 25mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|-----------------|--------------------------------|
| Cabinet fronts | Plain sheet metal sliding door |
| Weight | 107 kg |
| Width in G | 60 |
| Type of cabinet | Base cabinet |

| | |
|--|---|
| Depth in G | 28 |
| Handle positioning | top |
| Electronic locking system can be retrofitted | yes |
| Depth | 700 mm |
| Width | 1500 mm |
| Usable height | 663 mm |
| Height | 800 mm |
| ComfortClose | no |
| Version | for individual configuration |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1600 |
| Height adjustment interval | 25 |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Large-capacity cabinet |

Accessories

| | |
|-----------------------------------|-------------|
| Lock plate for GridLine Type GP21 | 914227 GP21 |
|-----------------------------------|-------------|