


Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Viewing window sliding door,
Height: 800mm****Order data**

Order number	942747 800
GTIN	4062406595883
Item class	9GI

Description**Version:**

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	60
Usable height	663 mm
Weight	107 kg
Electronic locking system can be retrofitted	yes

Type of cabinet	Base cabinet
Depth in G	28
Width	1500 mm
Height	800 mm
Depth	700 mm
ComfortClose	no
Cabinet fronts	Viewing window sliding door
Handle positioning	top
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Lock plate for GridLine Type GP21	914227 GP21
-----------------------------------	-------------