

Garant GRIDLINE

Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door, Height: 800mm



Order data

| | |
|--------------|---------------|
| Order number | 942765 800 |
| GTIN | 4062406595906 |
| Item class | 9GI |

Description

Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|-----------------|--------------|
| Depth | 700 mm |
| Usable height | 663 mm |
| Type of cabinet | Base cabinet |
| Depth in G | 28 |
| Weight | 125 kg |

| | |
|--|---|
| Handle positioning | top |
| Height | 800 mm |
| Width in G | 80 |
| Width | 2000 mm |
| ComfortClose | no |
| Electronic locking system can be retrofitted | yes |
| Cabinet fronts | Plain sheet metal sliding door |
| Version | for individual configuration |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1600 |
| Height adjustment interval | 25 |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Large-capacity cabinet |

Accessories

| | |
|-----------------------------------|-------------|
| Lock plate for GridLine Type GP21 | 914227 GP21 |
|-----------------------------------|-------------|