


Garant GRIDLINE

## Large-capacity / heavy-duty cabinet with Viewing window sliding door, Height: 800mm



### Order data

Order number	942767 800
GTIN	4062406595920
Item class	9GI

### Description

#### Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

**Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Handle positioning	top
Cabinet fronts	Viewing window sliding door
Width in G	80
Depth	700 mm
Usable height	663 mm

Depth in G	28
Height	800 mm
Width	2000 mm
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
ComfortClose	no
Weight	125 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

---

## Accessories

Lock plate for GridLine Type GP21	914227 GP21
-----------------------------------	-------------