

**Garant****Safety coupling Hose connection, Hose connection internal Ø (nominal bore): 13mm****Order data**

Order number	080372 13
GTIN	4062406596286
Item class	01A

**Description****Version:**

The GARANT safety shut-off is a high-performance coupling of galvanised steel, with extremely high flow rate capacity. New improved single-handed operation.

Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar. Satisfies the ISO standard 4414, ISO standard B and EN 983.

**Note:**

The GARANT series satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.

The GARANT series is suitable for the markets of Benelux, France, North America and Norway.

**Technical description**

Flow rate	2250 l/min
maximum operating pressure	16 bar
Hose connection internal Ø (nominal bore)	13 mm
Type of product	Coupling

