

Garant**Safety coupling Hose connection, Hose connection internal Ø (nominal bore): 8mm****Order data**

Order number	080372 8
GTIN	4062406596262
Item class	01A

Description**Version:**

The GARANT safety shut-off is a high-performance coupling of galvanised steel, with extremely high flow rate capacity. New improved single-handed operation.

Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar. Satisfies the ISO standard 4414, ISO standard B and EN 983.

Note:

The GARANT series satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.

The GARANT series is suitable for the markets of Benelux, France, North America and Norway.

Technical description

maximum operating pressure	16 bar
Flow rate	2250 l/min
Hose connection internal Ø (nominal bore)	8 mm
Type of product	Coupling

