

Electrically height-adjustable office desk white, Width: 1200mm



Order data

Order number	974030 1200
GTIN	4044917437234
Item class	91Q

Description

Version:

Office desk with electric height adjustment using controls. Base construction made up of solid T-leg frame on adjustable feet. Electrically height adjustable from **740– 1230 mm**. Motor with smooth start-up and smooth stop. Desk top melamine resin-coated with shock-resistant ABS edges. Speed of travel for height adjustment 25 mm/sec (unloaded).

Colour: Frame and top: white.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Weight	40 kg
Height adjustment range	740 - 1230 mm
Width	1200 mm
maximum load capacity	70 kg
Worktop thickness	19 mm
Depth	800 mm
Version	With electric height adjustment
Type of height adjustment	electrical

Insert thickness	19 mm
Type of product	Office desk