


Garant
GARANT Diabolo solid carbide milling cutter HPC, TiAlN, Ø e8 DC: 20mm

Order data

Order number	203372 20
GTIN	4045197597588
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide, specially for hard machining.

Application:

For profile milling as finishing.

(Plunge cutting only to shallow depths).

Technical description

Cutting edge Ø D _c	20 mm
No. of teeth Z	10
Feed f _z for side milling in steel < 65 HRC	0.03 mm
Shank Ø D _s	20 mm
Overall length L	135 mm
Flute length L _c	75 mm
Direction of infeed	horizontal and oblique
Shank	DIN 6535 HA to h6
Tolerance nominal Ø	e8
Helix angle	50 degrees
Corner chamfer angle	90 degrees
Series	Diabolo

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Helix angle characteristic	unequal spacing
Cutting width a_e for milling operation	$0.05 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	red
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	120 m/min	P
Steel < 50 HRC	suitable	115 m/min	H
Steel < 55 HRC	suitable	100 m/min	H
Steel < 60 HRC	suitable	90 m/min	H
Steel < 65 HRC	suitable	60 m/min	H
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------