



## Hose reel cast aluminum reel, Type: 20



### Order data

Order number	080074 20
GTIN	4030704030092
Item class	08A

### Description

#### Version:

Hose reels with **automatic pull-out and roll-up mechanism guided** by long life steel springs with **multiple stop points per revolution**.

Open hose roll-up reel with **aluminium cast body**, galvanised **pivoting run-out guide**, and robust **nylon-reinforced PVC hose**.

#### Application:

Suitable for air.

For increased ergonomics by relieving cable tension, and for ensuring tidiness and for avoiding the risk of accidents and injuries due to hoses lying on the ground.

### Technical description

usable hose length	20 m
Connection outlet	3/8 in
Material of hose	Poly vinyl chloride
maximum operating pressure	20 bar
Material of the housing	Aluminium

Connection inlet	3/8 in
Body width	380 mm
Body height	375 mm
Body depth	155 mm
Type of product	Hose reel