



Storage shelf, basic rack, Depth 400 mm, Height /storage shelf width: 1960/994mm



Order data

Order number	991930 1960/994
GTIN	4052941929557
Item class	95S

Description

Version:

Storage shelf for plug-in racking, galvanised. Rack stiles with cam grid permits easy insertion of storage shelves at 53 mm intervals. Storage shelves with double edge base with 10-fold longitudinal edge for particularly high stability and load capacity.

Maximum **shelf load 200 kg** per storage shelf.

Load per bay: for height 1960 mm 1000 kg, for 2490 mm 1200 kg, for 2967 mm 1400 kg.

Description:

Extension size:

Basic rack: Nominal length + 62 mm

add-on rack: Nominal length + 31 mm

Application:

Multi-functional racking system for all storage tasks. Can be extended retrospectively and fully converted thanks to a wide variety of accessories.

Supplied with:

Basic rack with cross braces, 4 floor anchors, 4 shims.

Extension rack without cross braces, with 2 floor anchors, 2 shims.

Note:

- **Screw-on base plates are supplied.**
- **Floor and wall fastenings are not included.**

- **Access from one side only due to use of cross brace.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**
- **Each third rack bay must be fitted with cross braces.**

Material: galvanised

Height: 1960 mm

Width: 994 mm

Depth: 400 mm

Assembled size basic rack width: 1056 mm

Number of shelves: 5

Storage shelf load capacity: 200 kg

Technical description

Width	994 mm
Rack access	single-sided
Number of shelves	5
Assembled size basic rack width	1056 mm
Plug-in assembly	yes
Height	1960 mm
Depth	400 mm
maximum bay load	1000 kg
Storage shelf load capacity	200 kg
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Shelf thickness	30 mm
Height adjustment interval	53 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 400 mm
Type of product	Storage shelf

Accessories

Storage shelf width×depth 994X400 mm	992011 994X400
Shims 2 mm Number of shims 5	992049 5
Floor anchor Type 2967	992047 2967
Shims 1 mm Number of shims 5	992048 5