

**Compressed air gun, Type: ALU****Order data**

Order number	080120 ALU
GTIN	4047322129213
Item class	08A

Description**Version:**

Universally applicable, up to 10 bar operating pressure. With 1.5 mm standard nozzle.

Supplied with:

Includes threaded coupling adapter No. 080157 size 1/4 inch and hose adapter 9 mm.

Note:

For suitable blow gun holders see No. 955750 ff.

maximum operating pressure: 10 bar

Flow rate at 6 bar: 250 l/min

Technical description

Type	ALU
maximum operating pressure	10 bar
Material	Aluminium
Flow rate at 6 bar	250 l/min

Accessories

Nozzle for ALU compressed air gun Type 150	080132 150
Nozzle for ALU compressed air gun Type VARIO	080132 VARIO
Nozzle for ALU compressed air gun Type SILENT1	080132 SILENT1
Nozzle for ALU compressed air gun Type SILENT2	080132 SILENT2