

**Wide-span add-on rack, Depth 800 mm, Height /storage shelf width:
2967/2570mm****Order data**

Order number	992207 2967/2570
GTIN	4052941773600
Item class	95S

Description**Version:**

Rack frame made from cold-rolled, high-strength galvanised steel with horizontal struts. Storage shelf levels adjustable at 53-mm intervals. Simple plug-in cross pieces ensure quick assembly. Storage shelf levels are made from segmented individual storage shelves.

Maximum **load per shelf:** 400 kg.

Bay load:

for height 1960 mm 1600 kg (for width 1994 mm), or 1250 kg (for width 2570 mm);

for height 2967 mm 2000 kg (for width 1994 mm), or 1800 kg (for width 2570 mm).

Condition for max. bay load:

Maximum height of lower storage level 200 mm, maximum compartment height 600 mm.

Description:**Extension size:**

Basic rack: Nominal length + 62 mm

add-on rack: Nominal length + 31 mm

Application:

Storage of bulky goods with light and medium loads. Access from both sides allows for short picking distances.

Supplied with:

10 longitudinal cross beams and 10 storage shelves each.

Note:

- **Floor anchoring is not included.**
- **Wide-span racking WR 3000 is compatible with storage shelf racking No. 991930 – 991967, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Material: galvanised

Assembled size add-on rack width: 2601 mm

Number of storage levels: 10

Shelf load capacity: 400 kg

Technical description

Assembled size add-on rack width	2601 mm
Number of storage levels	5
Application range	Wide-span racking
Height	2967 mm
Shelf load capacity	400 kg
Number of shelves	10
Shelf load capacity / maximum distributed shelf load (on metal)	400 kg
Shelf thickness	40 mm
Height adjustment interval	53 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 800 mm
Type of product	Wide-span racking

Accessories

Shelf, galvanised Width 2570 mm	992224 2570
---------------------------------	-------------