



Wide-span basic rack with steel panel, Depth 800 mm, Height /storage shelf width: 2500/2200mm



Order data

| | |
|--------------|------------------|
| Order number | 992306 2500/2200 |
| GTIN | 4052942007339 |
| Item class | 95S |

Description

Version:

Sturdy framework made from cold-rolled, high-strength galvanised steel support sections with horizontal and diagonal struts. Longitudinal crossbeams with screw-on 3-hook suspension brackets for a positive and frictional connection with rack supports. Each longitudinal crossbeam with 2 locking pins to prevent inadvertent lifting.

Steel panels made from Sendzimir-galvanised sheet metal are inserted into the longitudinal crossbeams with stepped profile. Load capacity per panel 150 kg with evenly distributed load. Complete set of panels with width of 200 and 300 mm.

Maximum **load per shelf:** up to 600 kg

Maximum **bay load capacity:**

for compartment height 500 mm: 3500 kg,

for compartment height 750 mm: 3000 kg,

for compartment height 1000 mm: 2700 kg,

for compartment height 1250 mm: 2300 kg,

for compartment height 1500 mm: 1800 kg.

Colour:

Stiles galvanised, longitudinal crossbeams RAL 5010 gentian blue **powder-coated**.

Note:

- **Floor anchorings are not included.**

· Supplied for self-assembly, saving freight costs. Delivered unassembled.

Type of installation: Plug-in racking

Number of storage levels: 3

Shelf load capacity: 600 kg

Technical description

| | |
|----------------------------|--|
| Shelf load capacity | 600 kg |
| Application range | Wide-span racking |
| Storage shelf depth | 800 mm |
| Number of storage levels | 3 |
| Height | 2500 mm |
| Rack access | double-sided |
| Shelf width | 2200 mm |
| Manufacturer's designation | WR600GF 2500x2200x800-3E steel pan. |
| Shelf thickness | 25 mm |
| Height adjustment interval | 50 mm |
| Type of installation | Plug-in racking |
| Product name attribute | Depth 800 mm |
| Type of product | Wide-span racking |

Accessories

| | |
|---|-------------|
| Steel panel storage level Width 2200 mm | 992354 2200 |
|---|-------------|