



Wide-span basic rack with steel panel, Depth 800 mm, Height /storage shelf width: 2500/1800mm



Order data

Order number	992306 2500/1800
GTIN	4052942007292
Item class	95S

Description

Version:

Sturdy framework made from cold-rolled, high-strength galvanised steel support sections with horizontal and diagonal struts. Longitudinal crossbeams with screw-on 3-hook suspension brackets for a positive and frictional connection with rack supports. Each longitudinal crossbeam with 2 locking pins to prevent inadvertent lifting.

Steel panels made from Sendzimir-galvanised sheet metal are inserted into the longitudinal crossbeams with stepped profile. Load capacity per panel 150 kg with evenly distributed load.

Complete set of panels with width of 200 and 300 mm.

Maximum **load per shelf:** up to 600 kg

Maximum **bay load capacity:**

- for compartment height 500 mm: 3500 kg,
- for compartment height 750 mm: 3000 kg,
- for compartment height 1000 mm: 2700 kg,
- for compartment height 1250 mm: 2300 kg,
- for compartment height 1500 mm: 1800 kg.

Colour:

Stiles galvanised, longitudinal crossbeams RAL 5010 gentian blue **powder-coated**.

Note:

- **Floor anchorings are not included.**

· **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Type of installation: Plug-in racking

Number of storage levels: 3

Shelf load capacity: 600 kg

Technical description

Shelf width	1800 mm
Height	2500 mm
Application range	Wide-span racking
Storage shelf depth	800 mm
Shelf load capacity	600 kg
Number of storage levels	3
Rack access	double-sided
Manufacturer's designation	WR600GF 2500x1800x800-3E steel pan.
Shelf thickness	25 mm
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 800 mm
Type of product	Wide-span racking

Accessories

Steel panel storage level Width 1800 mm	992354 1800
---	-------------