



Wide-span basic rack with chipboard shelf, Depth 800 mm, Height /storage shelf width: 2500/1800mm



Order data

Order number	992326 2500/1800
GTIN	4052942007131
Item class	95S

Description

Version:

Sturdy framework made from cold-rolled, high-strength galvanised steel support sections with horizontal and diagonal struts. Longitudinal crossbeams with screw-on 3-hook suspension brackets for a positive and frictional connection with rack supports. Each longitudinal crossbeam with 2 locking pins to prevent inadvertent lifting.

Compartment cover made of chipboard shelves is inserted between the longitudinal crossbeams. Quality: 22 mm, normally compressed.

Specified loads apply to evenly distributed loads.

Maximum **bay load capacity:**

- for compartment height 500 mm: 3500 kg,
- for compartment height 750 mm: 3000 kg,
- for compartment height 1000 mm: 2700 kg,
- for compartment height 1250 mm: 2300 kg,
- for compartment height 1500 mm: 1800 kg.

Colour:

Stiles galvanised, longitudinal crossbeams RAL 5010 gentian blue **powder-coated**.

Note:

- **Floor anchorings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Type of installation: Plug-in racking
Number of storage levels: 3
Shelf load capacity: 230 kg

Technical description

Shelf load capacity	230 kg
Storage shelf depth	800 mm
Height	2500 mm
Shelf width	1800 mm
Application range	Wide-span racking
Rack access	double-sided
Number of storage levels	3
Manufacturer's designation	WR600GF 2500x1800x800-3E chipboard shelf
Insert thickness	22 mm
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 800 mm
Type of product	Wide-span racking

Accessories

Chipboard shelf storage level Width 1800 mm	992364 1800
---	-------------