



## Wide-span extension rack with chipboard shelf, Depth 1050 mm, Height / storage shelf width: 2500/1800mm



### Order data

Order number	992329 2500/1800
GTIN	4052942007230
Item class	95S

### Description

#### Version:

Sturdy framework made from cold-rolled, high-strength galvanised steel support sections with horizontal and diagonal struts. Longitudinal crossbeams with screw-on 3-hook suspension brackets for a positive and frictional connection with rack supports. Each longitudinal crossbeam with 2 locking pins to prevent inadvertent lifting.

Compartment cover made of chipboard shelves is inserted between the longitudinal crossbeams. Quality: 22 mm, normally compressed.

Specified loads apply to evenly distributed loads.

#### Maximum **bay load capacity:**

- for compartment height 500 mm: 3500 kg,
- for compartment height 750 mm: 3000 kg,
- for compartment height 1000 mm: 2700 kg,
- for compartment height 1250 mm: 2300 kg,
- for compartment height 1500 mm: 1800 kg.

#### Colour:

Stiles galvanised, longitudinal crossbeams RAL 5010 gentian blue **powder-coated.**

#### Note:

- **Floor anchorings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Type of installation: Plug-in racking  
Number of storage levels: 3  
Shelf load capacity: 130 kg

## Technical description

Number of storage levels	3
Height	2500 mm
Shelf load capacity	130 kg
Storage shelf depth	1050 mm
Rack access	double-sided
Application range	Wide-span racking
Shelf width	1800 mm
Manufacturer's designation	WR600AF 2500x1800x1050-3E chipboard shelf
Insert thickness	22 mm
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 1050 mm
Type of product	Wide-span racking

## Accessories

Chipboard shelf storage level Width 1800 mm	992365 1800
---------------------------------------------	-------------