



## Wide-span extension rack with chipboard shelf, Depth 1050 mm, Height / storage shelf width: 3000/1800mm



### Order data

Order number	992329 3000/1800
GTIN	4052942007247
Item class	95S

### Description

#### Version:

Sturdy framework made from cold-rolled, high-strength galvanised steel support sections with horizontal and diagonal struts. Longitudinal crossbeams with screw-on 3-hook suspension brackets for a positive and frictional connection with rack supports. Each longitudinal crossbeam with 2 locking pins to prevent inadvertent lifting.

Compartment cover made of chipboard shelves is inserted between the longitudinal crossbeams. Quality: 22 mm, normally compressed.

Specified loads apply to evenly distributed loads.

#### Maximum **bay load capacity:**

for compartment height 500 mm: 3500 kg,  
for compartment height 750 mm: 3000 kg,  
for compartment height 1000 mm: 2700 kg,  
for compartment height 1250 mm: 2300 kg,  
for compartment height 1500 mm: 1800 kg.

#### Colour:

Stiles galvanised, longitudinal crossbeams RAL 5010 gentian blue **powder-coated.**

#### Note:

- **Floor anchoring is not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

- **If forklift trucks are used for loading, a stile protrusion of 500 mm is required.**

Type of installation: Plug-in racking

Number of storage levels: 4

Shelf load capacity: 130 kg

## Technical description

Number of storage levels	4
Rack access	double-sided
Shelf load capacity	130 kg
Height	3000 mm
Shelf width	1800 mm
Storage shelf depth	1050 mm
Application range	Wide-span racking
Manufacturer's designation	WR600AF 3000x1800x1050-4E chipboard shelf
Insert thickness	22 mm
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 1050 mm
Type of product	Wide-span racking

## Accessories

Chipboard shelf storage level Width 1800 mm	992365 1800
---	-------------