

**Pallet basic rack, Depth 1100 mm, Height: 4700mm****Order data**

Order number	992410 4700
GTIN	4052941835735
Item class	95S

**Description****Version:**

Pallet racking made of cold-rolled high-strength steel profile frame. High stiffness of the frame due to special design: Bolted to a sturdy framework with horizontal and diagonal struts. Longitudinal crossbeams with welded-on 5-hook suspension brackets for a positive and frictional connection with rack supports. Including floor anchors.

**Supplied with:**

**Basic rack:** 2 profile frames, longitudinal cross beams, 8 floor anchors, 2 safe working load signs.

**Extension rack:** 1 profile frame, longitudinal cross beams, 4 floor anchors.

**Colour:**

Stiles galvanised, beams RAL 5010 gentian blue **powder-coated**.

**Note:**

- **On uneven floors we recommend additional shim plates.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Type of installation: Plug-in racking

Compartment width: 2700 mm

Cross beam height: 100 mm

lower compartment height: 1400 mm

Number of longitudinal cross beams: 6

Number of storage level: 3

maximum bay load: 7200 kg

## Technical description

Width	2700 mm
Height	4700 mm
Application range	Pallet racking
Number of storage level	3
Depth	1100 mm
Compartment width	2700 mm
maximum bay load	7200 kg
Cross beam height	100 mm
Number of longitudinal cross beams	6
lower compartment height	1400 mm
Shelf load capacity / maximum distributed shelf load (on metal)	2400 kg
To take pallets with load capacity	800 kg
Height adjustment interval	50 mm
Type of installation	Plug-in racking
Product name attribute	Depth 1100 mm
Type of product	Pallet racking

## Accessories

Locking pins, 12 pieces Number of locking pins 12	992501 12
Frame stiles Height 4700 mm	992461 4700
Pair of longitudinal cross beams Width 2700 mm	992482 2700
Floor anchor Number of floor anchors 2	992545 2