



Boring bar set, steel, without IC, right-hand, Type: 1



Order data

Order number	255160 1
GTIN	4062406609450
Item class	29W

Technical description

ISO code toolholder	S16R PCLNR09; S20S PDUNR11; S16M PWLNR06
Overall length L	200 mm
Overall length L	250 mm
Overall length L	150 mm
Centre offset L ₃	11 mm
Centre offset L ₃	13 mm
Centre offset L ₃	11 mm
suitable indexable insert	CN.. 09T3.; DN.. 1104.; WN.. 0604..
Clamping height L ₂	15.25 mm
Clamping height L ₂	19 mm
Clamping height L ₂	15.25 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm

Minimum pre-drill $\varnothing D_{\min}$	25 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Spare part	259981 10
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Tool material	Steel
Through-coolant	no
Type of product	Boring bar