



Boring bar set, steel, without IC, right-hand, Type: 2



Order data

Order number	255160 2
GTIN	4062406609467
Item class	29W

Technical description

Clamping height L_2	19 mm
Clamping height L_2	24 mm
Clamping height L_2	19 mm
Overall length L	250 mm
Overall length L	250 mm
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
Minimum pre-drill $\varnothing D_{min}$	32 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
Centre offset L_3	13 mm
Centre offset L_3	17 mm
Centre offset L_3	13 mm

suitable indexable insert	CN.. 09T3.; DN.. 1104.; WN.. 0604..
ISO code toolholder	S20S PCLNR09; S25S PDUNR11; S20Q PWLNR06
Spare part	259981 11
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Tool material	Steel
Through-coolant	no
Type of product	Boring bar