



## Boring bar set, steel, without IC, right-hand, Type: 3



### Order data

Order number	255160 3
GTIN	4062406609474
Item class	29W

### Technical description

suitable indexable insert	CN.. 1204.; DN..1506.; WN.. 0804..
Overall length L	250 mm
Overall length L	250 mm
Overall length L	200 mm
Centre offset L <sub>3</sub>	17 mm
Centre offset L <sub>3</sub>	22 mm
Centre offset L <sub>3</sub>	17 mm
Clamping height L <sub>2</sub>	24 mm
Clamping height L <sub>2</sub>	31 mm
Clamping height L <sub>2</sub>	24 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Minimum pre-drill $\varnothing D_{\min}$	40 mm

Minimum pre-drill $\varnothing D_{\min}$	32 mm
ISO code toolholder	S25S PCLNR12; S32S PDUNR15; S25R PWLNR08
Spare part	259981 12
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Tool material	Steel
Through-coolant	no
Type of product	Boring bar