



Boring bar set, steel, without IC, left-hand, Type: 3



Order data

Order number	255161 3
GTIN	4062406609504
Item class	29W

Technical description

Clamping height L ₂	24 mm
Clamping height L ₂	31 mm
Clamping height L ₂	24 mm
ISO code toolholder	S25S PCLNL12; S32S PDUNL15; S25R PWLNL08
Overall length L	250 mm
Overall length L	250 mm
Overall length L	200 mm
suitable indexable insert	CN.. 1204..; DN..1506..; WN.. 0804..
Centre offset L ₃	17 mm
Centre offset L ₃	22 mm
Centre offset L ₃	17 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm

Minimum pre-drill $\varnothing D_{\min}$	40 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Spare part	259981 12
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Tool material	HSS
Through-coolant	no
Type of product	Boring bar