



Boring bar set, steel, without IC, left-hand, Type: 2



Order data

Order number	255161 2
GTIN	4062406609498
Item class	29W

Technical description

suitable indexable insert	CN.. 09T3.; DN.. 1104.; WN.. 0604..
Minimum pre-drill $\varnothing D_{min}$	25 mm
Minimum pre-drill $\varnothing D_{min}$	32 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
ISO code toolholder	S20S PCLNL09; S25S PDUNL11; S20Q PWLNL06
Overall length L	250 mm
Overall length L	250 mm
Overall length L	180 mm
Centre offset L_3	13 mm
Centre offset L_3	17 mm
Centre offset L_3	13 mm
Clamping height L_2	19 mm

Clamping height L ₂	24 mm
Clamping height L ₂	19 mm
Spare part	259981 11
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Tool material	HSS
Through-coolant	no
Type of product	Boring bar