



## Boring bar set, steel, without IC, left-hand, Type: 1



### Order data

Order number	255161 1
GTIN	4062406609481
Item class	29W

### Technical description

ISO code toolholder	S16R PCLNL09; S20S PDUNL11; S16M PWLNL06
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Overall length L	200 mm
Overall length L	250 mm
Overall length L	150 mm
Centre offset $L_3$	11 mm
Centre offset $L_3$	13 mm
Centre offset $L_3$	11 mm
suitable indexable insert	CN.. 09T3.; DN.. 1104.; WN.. 0604..
Clamping height $L_2$	15.25 mm

Clamping height L <sub>2</sub>	19 mm
Clamping height L <sub>2</sub>	15.25 mm
Spare part	259981 10
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Tool material	HSS
Through-coolant	no
Type of product	Boring bar