

Garant GRIDLINE

Height adjustable wheel set set of 2 pieces, Type: 1



Order data

Order number	927206 1
GTIN	4062406605285
Item class	9GG

Description

Version:

Manual height adjustment as a plug-in module in the feet of the workbench including wheels with \varnothing 125 mm. Fibre shields prevent the castors jamming. Optimally smooth running due to high-quality ball bearings, with treadless polyurethane tyres, minimal rolling resistance and low noise emitted in motion. The wheel set has a maximum load capacity of 100 kg and must not be fitted to support legs with a height of 900 mm. Not possible in conjunction with Ready-to-go workbenches. Height adjustment at 25 mm intervals.

Supplied with:

Set consisting of 2 plug-in modules, suitable for 1 support leg or 2 feet. Set consisting of 2 plug-in modules with **fixed wheels**, including fastenings.

Colour:

Height adjustment RAL 7035 light grey, **powder-coated**. Wheels galvanised, not configurable.

Note:

The fitting of wheels increases the working height of the workbench by 150 mm. You will need 2 sets for one workbench with 2 support legs.

When calculating the load capacity of the workbench, only 3 wheels may be taken into account. The maximum load capacity of a workbench is 150 kg.

Technical description

Width	45 mm
Height adjustment range	150 mm
Height	325 mm
Depth	95 mm
Fixed wheel Ø	125 mm
Load capacity per wheel	50 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Roller