



Boring bar set, steel, with IC, right-hand, Type: SET1



Order data

Order number	265155 SET1
GTIN	4062406609603
Item class	29W

Technical description

Centre offset L ₃	6 mm
Centre offset L ₃	4 mm
Centre offset L ₃	9 mm
Centre offset L ₃	6.5 mm
Pack of insert screws	269028 7
Neck width L ₄	10 mm
Neck width L ₄	8 mm
Neck width L ₄	8 mm
Neck width L ₄	6 mm
Head length L ₁	22 mm
Head length L ₁	22.5 mm

Head length L ₁	27.5 mm
Head length L ₁	27 mm
suitable indexable insert	CC.. 0602..
suitable indexable insert	DC.. 0702..
Minimum pre-drill Ø D _{min}	12 mm
Minimum pre-drill Ø D _{min}	11 mm
Minimum pre-drill Ø D _{min}	15.5 mm
Minimum pre-drill Ø D _{min}	8 mm
Clamping height L ₂	11 mm
Clamping height L ₂	9 mm
Clamping height L ₂	9 mm
Clamping height L ₂	7 mm
Overall length L	100 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
ISO code toolholder	A0810J SCLCR/L06
ISO code toolholder	A0608H SCLCR/L06
ISO code toolholder	A0810H SDUCR/L07
ISO code toolholder	A1012K SDUCR/L07
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar steel Shank Ø / insert size 0608/06 mm	260032 0608/06
---	----------------

Boring bar steel Shank Ø / insert size 0810/06 mm	260032 0810/06
Boring bar steel Shank Ø / insert size 1012/06 mm	260032 1012/06
Boring bar steel Shank Ø / insert size 1216/06 mm	260032 1216/06
Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8