

**Boring bar set, steel, without IC, right-hand, Type: SET1****Order data**

Order number	265157 SET1
GTIN	4062406612429
Item class	29W

Description**Version:**

Without through-coolant feed.

Technical description

Head length L_1	22.5 mm
Head length L_1	27 mm
Head length L_1	22 mm
Head length L_1	27.5 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm

ISO code toolholder	S0810H SCLCR06
ISO code toolholder	S0810J SCLCR06
ISO code toolholder	S0810J SCLCR06
ISO code toolholder	S1216K SDUCR07
Clamping height L ₂	9 mm
Clamping height L ₂	11 mm
Clamping height L ₂	9 mm
Clamping height L ₂	7 mm
Centre offset L ₃	6.5 mm
Centre offset L ₃	6 mm
Centre offset L ₃	4 mm
Centre offset L ₃	9 mm
Overall length L	125 mm
Overall length L	110 mm
Overall length L	100 mm
Overall length L	100 mm
Neck width L ₄	6 mm
Neck width L ₄	8 mm
Neck width L ₄	10 mm
Neck width L ₄	8 mm
suitable indexable insert	CC.. 0602..
suitable indexable insert	DC.. 0702..
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8