



Hose reel cast aluminum reel, Type: 20SCS



Order data

Order number	080074 20SCS
GTIN	4030704033093
Item class	08A

Description

Version:

Hose reels with **automatic pull-out and roll-up mechanism guided** by long life steel springs with **multiple stop points per revolution**.

Open hose roll-up reel with **aluminium cast body**, galvanised **pivoting run-out guide**, and robust **nylon-reinforced PVC hose**. With patented SCS controlled automatic roll-up mechanism for avoidance of damage and injuries.

Application:

Suitable for air.

For increased ergonomics by relieving cable tension, and for ensuring tidiness and for avoiding the risk of accidents and injuries due to hoses lying on the ground.

Technical description

Connection outlet	3/8 in
Connection inlet	3/8 in
usable hose length	20 m
Material of hose	Poly vinyl chloride

SCS automatic roll-up drum	yes
maximum operating pressure	20 bar
Material of the housing	Aluminium
Body height	375 mm
Body depth	155 mm
Body width	380 mm
Type of product	Hose reel