

Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 8mm



Order data

| | |
|--------------|---------------|
| Order number | 085925 8 |
| GTIN | 4045197153555 |
| Item class | 08Q |

Description

Version:

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

| | |
|-----------------------------------|-----------------------------|
| maximum temperature resistance | 220 °C |
| Nominal clamping force | 3 N |
| Height | 12 mm |
| Material of the surface | galvanised |
| Ø | 8 mm |
| maximum shortening dimension rear | 3 mm |
| Material of the magnet core | AlNiCo |
| Type of product | Cylindrical clamping magnet |

