

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 20/07mm**

**Order data**

Order number	260308 20/07
GTIN	4062406602246
Item class	21T

**Technical description**

Overall length L	125 mm
Head length L <sub>1</sub>	24 mm
ISO code toolholder	SDJCR/L 2020K07
Insert size	7 mm
Shank size	20 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 22
Functional width L <sub>4</sub>	24 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500