

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 16/07mm****Order data**

Order number	260308 16/07
GTIN	4062406602239
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	20 mm
Head length L <sub>1</sub>	22 mm
Shank size	16 mm
Pack of insert screws	269028 22
suitable indexable insert	DC.. 0702..
Overall length L	100 mm
ISO code toolholder	SDJCR/L 1616H11
Insert size	7 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500