

Garant**Screw-on toolholder, left-hand, Shank / insert size: 16/07mm****Order data**

Order number	260309 16/07
GTIN	4062406602253
Item class	21T

Technical description

Shank size	16 mm
Overall length L	100 mm
Functional width L ₄	20 mm
Insert size	7 mm
ISO code toolholder	SDJCR/L 1616H07
suitable indexable insert	DC.. 0702..
Head length L ₁	22 mm
Pack of insert screws	269028 22
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500