

Deep pot magnet with toleranced dimensions, AlNiCo, Ø: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 085925 10 |
| GTIN | 2050000965104 |
| Item class | 08Q |

Description

Version:

- **Shielded bar magnet with magnetic core of AlNiCo.**
- **Fit tolerance on the external Ø h6.**
- **Temperature-resistant up to maximum 220 °C.**

Application:

For clamping, assembling, incorporation by pressing in, gluing or encapsulating.

Technical description

| | |
|-----------------------------------|-----------------------------|
| Nominal clamping force | 5 N |
| Ø | 10 mm |
| maximum temperature resistance | 220 °C |
| Height | 16 mm |
| Material of the surface | galvanised |
| maximum shortening dimension rear | 6 mm |
| Material of the magnet core | AlNiCo |
| Type of product | Cylindrical clamping magnet |

