

**Flat magnet with hook, Neodymium, Shank size: E1070/NEO****Order data**

Order number	085974 E1070/NEO
GTIN	5012095619390
Item class	08Q

Description**Version:**

Freely rotatable by 360° around the magnetic base and 180° pivotable.

Application:

Ideal for hanging up various items without screws or nails.

Technical description

Ø	25 mm
Weight	38 g
Height	65 mm
Nominal clamping force	180 N
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

