

**Flat magnet with carabiner, Neodymium, Shank size: E1066/NEO****Order data**

Order number	085975 E1066/NEO
GTIN	5012095617716
Item class	08Q

**Description****Version:**

Temperature-resistant up to maximum 80°C.

**Application:**

Ideal for holding and hanging up ropes, wires and cables, etc.

**Technical description**

Ø	28 mm
Nominal clamping force	200 N
maximum temperature resistance	80 °C
Height	14 mm
Weight	30 g
Material of the magnet core	Neodymium
Type of product	Flat gripper magnet

