



## Assortment box of standard screw fastenings, Shank size: SET1



### Order data

|              |               |
|--------------|---------------|
| Order number | P08024 SET1   |
| GTIN         | 4047322217460 |
| Item class   | 08A           |

### Description

#### Version:

Brass turned parts assortment box, working pressure max. 25 bar, operating temperature max. 150°C.

Handy, robust, high-quality plastic assortment box with the most common sleeves, double nipples, reducing bushes, connection screws and locknuts from our brass turned parts range. A total of 35 different types of small parts are presented clearly in 21 plastic boxes. The inserts can be taken out and stored individually in the box. All inserts are labelled with the item numbers of the stored parts.

#### Content:

30 screw-in hose sleeves: G 1/4-6; G 1/4-9; G 3/8-6; G 3/8-9; G 1/2-9; G 1/2-13

38 double nipples: G 1/8 × G 1/8; G 1/8 × G 1/4; G 1/4 × G 1/4; G 1/4 × G 3/8; G 3/8 × G 3/8; G 3/8 × G 1/2; G 1/2 × G 1/2; G 1/2 × G 3/4

19 reducing bushes G 1/4 o. × G 1/8 i.; G 3/8 o. × G 1/4 i.; G 1/2 o. × G 3/8 i.; G 3/4 o. × G 1/2 i.

18 sleeves G 1/8; G 1/4; G 3/8; G 1/2

connection screws G 1/8; G 1/4; G 3/8; G 1/2

15 double hose couplings 6, 9, 13 mm

20 locknuts G 1/8; G 1/4; G 3/8; G 1/2

Thread adhesive 10 ml

1 PTFE sealing tape

### Technical description

Material

Brass