

KÄRCHER**Scrubber dryer, Type: BR4522CBP****Order data**

Order number	078002 BR4522CBP
GTIN	4054278440064
Item class	07C

Description**Version:**

Ideal for large, restricted areas: very manoeuvrable, battery-powered BR 45/22 Bp Pack scrubber dryer. With rotating roller brush head and KART technology.

Handheld floor cleaning machine for a wide variety of applications and various surface sizes.

Optionally as a mains-powered or battery-powered version. High productivity and economical consumption.

Technical description

max. area coverage	1800 m ² /h
Working width, brushes	450 mm
Weight including accessories	51.7 kg
Length	970 mm
Volume of the fresh water tank	22 l
min. brush contact pressure	100 - 150 g/cm ³
Brush speed	750 - 1000 min ⁻¹

Volume of the dirty water tank	22 l
Power consumption	550 W
Width	550 mm
Height	1115 mm
Working width, suction	500 mm
Battery voltage	25.2 V
Battery capacity	42 Ah
Power supply	Rechargeable battery-powered
Type of product	Floor cleaning device