

KÄRCHER
Scrubber dryer, Type: BR4010CADV

Order data

Order number	078001 BR4010CADV
GTIN	4039784541498
Item class	07C

Description
Version:

The BR 40/10 C: the most cost-effective machine of its class. The compact and powerful machine has a working width of 400 mm and a tank volume of 10 l. The Advance variant has additional transport wheels and brush contact pressure adjustment.

Handheld floor cleaning machine for a wide variety of applications and various surface sizes. Optionally as a mains-powered or battery-powered version. High productivity and economical consumption.

Working width, brushes: 400 mm

Working width, suction: 400 mm

Length: 520 mm

Width: 470 mm

Height: 1150 mm

max. area coverage: 400 m²/h

Technical description

Working width, brushes	400 mm
Weight including accessories	30 kg

Width	470 mm
Volume of the dirty water tank	10 l
Power consumption	2300 W
Working width, suction	400 mm
Length	520 mm
Height	1150 mm
Volume of the fresh water tank	10 l
min. brush contact pressure	100 g/cm ³
max. area coverage	400 m ² /h
Brush speed	1100 min ⁻¹
Mains frequency	50 Hz
AC supply voltage	220 - 240 V
Power supply	Mains operated
Type of product	Floor cleaning device