



## LED desk lamp, Shank size: 10



### Order data

Order number	081408 10
GTIN	4260131239168
Item class	08C

### Description

#### Version:

Innovative "Comet" table lamp with gesture control at the lamp head for switching on and off and dimming function. In addition, the colour temperature can be changed as required using a second sensor, also by gesture control. The two sensors react as soon as the user holds their hand below the respective sensor. The slim, elegant silver anodised aluminium casing with its flexible neck sheathed in classic black fabric makes the lamp blend in perfectly with modern office equipment.

- **Sturdy table base.**
- **Uniformly homogeneous and low-reflection 120° illumination.**
- **The light colour can be changed from cold white to warm white using the sensor on the lamp head.**
- **Steplessly dimmable, also by gesture control at the lamp head.**
- **Non-dazzling and flicker-free.**

### Technical description

Bulb	LED lamp
Colour temperature	2700 - 5500 K
Light output	10 W

Power supply	Mains operated
Light colour	warm white
Light colour	cold white
Light colour	neutral white
Overall height	900 mm
Illumination	960 lm
Lamp head width	30 mm
Lamp head depth	210 mm
Lamp head height	10 mm
Type of product	Desk lamp / workstation lamp