



LED workstation lamp with gesture control, Type: 10



Order data

Order number	081409 10
GTIN	4260131239366
Item class	08C

Description

Version:

Innovative workstation lamp **with gesture control** at the lamp head for switching on and off and dimming function. Colour temperature can be changed as required. The lamp can be used in various different fields of application.

- **Strong magnetic base.**
- **Uniform, homogeneous and low-reflection 120° illumination.**
- **Non-dazzling and flicker-free.**
- **The light colour can be changed from cold white to warm white using the sensor on the lamp head.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 250-V power supply unit.

Note:

Suitable table clamps and magnetic holders can be found under 081418/081419.

Technical description

Light output	10 W
IP Index of Protection	IP 65
Lamp head depth	210 mm
Magnetic base Ø	66 mm
Weight	760 g
Lamp head height	10 mm
Lamp head width	30 mm
Colour temperature	2700 - 5500 K
Overall height	750 mm
Illumination	960 lm
Power supply	Mains-powered
Type of product	Desk lamp / workstation lamp