



HCT digital caliper with Bluetooth, Measuring range: 150mm



Order data

Order number	412790 150
GTIN	4062406629434
Item class	42A

Description

Version:

Digital caliper with **Bluetooth 5.0**. Easy-to-read LCD display. Very long battery running time due to modern energy-efficient measurement system. Easy-grip surface. Measuring faces are precision lapped. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID). Programmable automatic shut-down and programmable automatic reaching of SLEEP mode via the HCT app.

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Depth gauge	rectangular 3.7×1.3
Reversible reading	mm / inch
Power supply	Battery-powered
Measuring range	0 - 150 mm
Wireless application	HCT Mobile App
Wireless application	HID (Human Interface Device)
Wireless application	HCT Windows app
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 No. CR2032

Standard	ISO 13385
Jaw length	40 mm
Scale divisions	0.0005 in
Series	HCT
Battery type	Button cell
Depth gauge available	yes
Scale divisions	0.01 mm
Calibration	A1
Measurement deviation E MPE	± 0.03 mm
Interface	Bluetooth interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236