



HCT digital depth gauge with Bluetooth, Measuring range: 300mm



Order data

Order number	418743 300
GTIN	4062406629489
Item class	42A

Description

Version:

Measured result is displayed in easy-to-read digits. The measuring faces are precision lapped. Bluetooth 5.0. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS and the HCT Windows app. Can also be used via a Human Interface Device (HID).

Supplied with:

1 battery No. 081560 size CR2032.

Technical description

Reversible reading	0.0005 in
Calibration	A1
Series	HCT
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Cross-section measuring beam	16×4 mm
Power supply	Battery-powered
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032

Bridge length	100 mm
Reversible reading	0.01 mm
Interface	Bluetooth interface
Measuring range	0 - 300 mm
Battery type	Button cell
Measurement deviation E MPE	± 0.04 mm
Standard	ISO 13385
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

Services

CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300
DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300

Accessories

Screw for depth gauge holder	412236
------------------------------	--------